

Pneumatic muffler

U-3/4

Part number: 2311

FESTO



Data sheet

Feature	Value
Mounting position	Any
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate with respect to atmosphere	17600 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	85 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	83 g
Pneumatic connection	G3/4
Cushioning insert material	PE
Note on materials	RoHS-compliant