

Clamping sleeve
EAMH-110-14-C34
Part number: 2429557



Data sheet

Feature	Value
Size	110
Mounting position	Any
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	31.8 kgmm ²
Product weight	219 g
Note on materials	RoHS-compliant