

Self-aligning quick coupling CRFK-M20X1,5

Part number: 2545677

FESTO



Data sheet

Feature	Value
Size	M20x1.5
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-20 °C...100 °C
Max. load capacity	9 kN
Product weight	1280 g
Note on materials	RoHS-compliant
Housing material	High-alloy stainless steel
Threaded bolt material	High-alloy stainless steel
Cap material	EPDM
Nut material	High-alloy stainless steel