

Counter bearing
EAMG-U1-70
Part number: 2598638

FESTO



Data sheet

Feature	Value
Size	70
Mounting position	Any
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Product weight	74 g
Note on materials	RoHS-compliant