


Axial kit EAMM-A-D50-80P-S1

Part number: 2734289



Data sheet

Feature	Value
Nominal length	80.7 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	17 Nm
Product weight	890 g
Interface code, actuator	D50
Interface code, motor in	80P
Note on materials	RoHS-compliant