


Axial kit
EAMM-A-D50-80G-S1
Part number: 2734291



Data sheet

Feature	Value
Nominal length	93.4 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	17 Nm
Product weight	1190 g
Interface code, actuator	D50
Interface code, motor in	80G
Note on materials	RoHS-compliant