


Sub-base
VABP-S1-2V1G-G38-2
Part number: 2738671

FESTO



Data sheet

Feature	Value
Width	54 mm
Function port 32	G1/4
Function port 34	G1/4
Pneumatic connection 22	Sub-base G3/8
Pneumatic connection 44	Sub-base G3/8
Mounting position	Any
Operating pressure	0 bar...16 bar
Standard nominal flow rate	2000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [6:4:4]
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Product weight	1950 g
Pilot air port 14	G1/8
Pneumatic connection 2	G3/8
Pneumatic connection 4	G3/8
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy
O-ring material	NBR
Material of screws	Steel