

**Parallel kit**  
**EAMM-U-70-D50-70A-96-S1**  
Part number: 2756078

**FESTO**



**Data sheet**

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Size                     | 70                    |
| Mounting position        | Any                   |
| Gear ratio               | 1:1                   |
| Max. rotational speed    | 5000 rpm              |
| LABS (PWIS) conformity   | VDMA24364 zone III    |
| Storage temperature      | -25 °C...60 °C        |
| Relative air humidity    | 0 - 95 %              |
| Degree of protection     | IP65                  |
| Ambient temperature      | -10 °C...60 °C        |
| Mass moment of inertia   | 118 kgmm <sup>2</sup> |
| No-load driving torque   | 0.18 Nm               |
| Transferable torque      | 7 Nm                  |
| Product weight           | 1730 g                |
| Interface code, actuator | D50B                  |
| Interface code, motor in | 70A                   |
| Note on materials        | RoHS-compliant        |