

Clamping sleeve EAMH-86-9-C27.3

Part number: 2789221



Data sheet

Feature	Value
Size	86
Mounting position	Any
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	11.6 kgmm ²
Product weight	116 g
Note on materials	RoHS-compliant