

Flange mounting EAHH-V2-40-R1

Part number: 2827588

FESTO



Data sheet

| Feature | Value |
|--|---|
| Size | 40 |
| Based on norm | ISO 15552 |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Statically installed element, no meaningful evaluation possible according to ISO 14644-1 |
| Max. load capacity | 3 kN |
| Product weight | 275 g |
| Note on materials | RoHS-compliant |
| Plate material | High-alloy stainless steel |
| Material of screws | High-alloy stainless steel |