


Sub-base
NAUE-1/4-NPT-1-ISO
Part number: 30427

FESTO



Data sheet

Feature	Value
Operating pressure	0 bar...16 bar
Certification	UL - Recognized (OL)
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Type of mounting	With through-hole
Pilot air port 12	1/8 NPTF
Pilot air port 14	1/8 NPTF
Pneumatic connection 1	1/4 NPTF
Pneumatic connection 2	1/4 NPTF
Pneumatic connection 3	1/4 NPTF
Pneumatic connection 4	1/4 NPTF
Pneumatic connection 5	1/4 NPTF