


# Plug socket with cable KMV-1-230AC-5

Part number: 30942

**FESTO**



## Data sheet

Feature	Value
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	320 g
Electrical connection	Socket Form B
Nominal operating voltage AC	230 V
Reverse polarity protection	for all electrical connections
Protective earth connection	Available
Cable length	5 m
Cable diameter	6 mm
Cable design	3 x 0.75 mm <sup>2</sup>
Degree of protection	IP67 as per IEC 60529
Ambient temperature	-20 °C...80 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	PVC
Housing material	PC
Material of pin contacts	Bronze