

Pneumatic protective conduit fitting MKGV-23-M32-B

Part number: 3152612

FESTO



Data sheet

Feature	Value
Mounting position	Any
Pack size	100
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Ambient temperature	-40 °C...100 °C
Type of mounting	With external thread
Note on materials	RoHS-compliant
Material of pneumatic fitting	PA