

Clevis foot
LSNG-63
Part number: 31743



Data sheet

Feature	Value
Size	63
Based on norm	VDMA 24562
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...150 °C
Max. load capacity	4 kN
Product weight	541 g
Note on materials	RoHS-compliant
Mounting material	Spherulitic graphite iron
Rod end bearing material	Steel PTFE