

Clevis foot
LBG-40
Part number: 31762



Data sheet

Feature	Value
Size	40
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 1% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper by mass are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils are excluded
Ambient temperature	-40 °C...150 °C
Max. load capacity	1,5 kN
Product weight	300 g 10.57 oz
Note on materials	RoHS-compliant
Mounting material	Cast stainless steel
Bolt material	Case-hardened steel
Fuse material	Spring steel