

**Clevis foot**  
**LBG-80**  
Part number: 31765



**Data sheet**

Feature	Value
Size	80
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	6 kN
Product weight	1050 g
Note on materials	RoHS-compliant
Mounting material	Spherulitic graphite iron
Bolt material	Case-hardened steel
Fuse material	Spring steel