

Clevis foot
LBG-100
Part number: 31766



Data sheet

| Feature | Value |
|--|--|
| Size | 100 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils |
| Ambient temperature | -40 °C...150 °C |
| Max. load capacity | 9 kN |
| Product weight | 1375 g |
| Note on materials | RoHS-compliant |
| Mounting material | Spherulitic graphite iron |
| Bolt material | Case-hardened steel |
| Fuse material | Spring steel |