

**Non return valve**  
**H-1/8-A/I**  
Part number: 3324

**FESTO**



**Data sheet**

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8
Type of mounting	Line installation
Normal nominal flow rate (normalized to DIN 1343)	280 l/min
Operating pressure	0.04 MPa...0.8 MPa 0.4 bar...8 bar
Ambient temperature	-10 °C...60 °C
Housing material	Brass
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	-10 °C...60 °C
Product weight	21 g
Seals material	NBR