

Foot mounting DAMH-Q12-8

Part number: 3371841

FESTO



Data sheet

Feature	Value
Size	8
Mounting position	Any
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Max. tightening torque	1 Nm
Product weight	40 g
Type of mounting	With through-hole
Note on materials	RoHS-compliant
Bracket material	Steel, galvanized