

Clevis foot LNG-40

Part number: 33891



Data sheet

Feature	Value
Size	40
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...80 °C
Max. load capacity	1.5 kN
Product weight	161 g
Note on materials	RoHS-compliant
Mounting material	Tempered steel
Material of bearing	PA