

Solenoid coil MSFG-42-OD

Part number: 34413

FESTO



Data sheet

Feature	Value
Mounting position	Any
Switching position indication	no
Min. pick-up time	10 ms
Duty cycle	100%
Coil characteristics	42 V DC: 5.5 W
Permissible voltage fluctuations	+/- 10 %
LABS (PWIS) conformity	VDMA24364-C1-L
Degree of protection	IP65
Ambient temperature	-5 °C...40 °C
Max. tightening torque of socket	0.4 Nm
Product weight	55 g
Electrical connection	3-pin Plug flags with connection diagram as per Festo standard for MSSD-F
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Solenoid coil material	Duroplast Copper Steel
Material of winding	Copper