

Guide unit FENG-80- -GF

Part number: 34485

FESTO



Data sheet

Feature	Value
Size	80
Stroke	10 mm...500 mm
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Explosion prevention and protection	Observe the information on the certificate
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Displacement force	70 N
Additional moving mass per 10 mm stroke	76 g
Basic weight with 0 mm stroke	10720 g
Additional weight per 10 mm stroke	76 g
Center of gravity of moving mass with 0 mm stroke	54 mm
Center of gravity of moving mass with 10 mm stroke	3.9 mm
Type of mounting	With internal thread
Note on materials	RoHS-compliant
Material of guide component	High-alloy steel
Housing material	Wrought aluminum alloy, anodized
Material of yoke plate	Tempered steel