

Vacuum suction cup

VAS-8-M5-NBR

Part number: 34588

FESTO



Data sheet

| Feature | Value |
|---|--|
| Nominal width | 2 mm |
| Suction cup diameter | 8 mm |
| Effective suction cup diameter | 5.5 mm |
| Connection position | Top |
| Suction cup shape | Round, flat |
| Operating pressure | -0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 psi...0 psi |
| Nominal operating pressure | -0.07 MPa -0.7 bar -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::] |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | -20 °C...80 °C |
| Breakaway force at 70% vacuum | 1.6 N |
| Holding force at nominal operating pressure | 1.6 N |
| Mounting thread | M5 |
| Suction cup mounting | M5 |
| Vacuum connection | M5 |
| Color | Black |
| Shore hardness | 60 +/- 5 |
| Material of screwed plug | Brass |
| Note on materials | RoHS-compliant |
| Suction cup material | NBR |