


Pneumatic timer
VZOA-3-1/4
Part number: 3464



Data sheet

Feature	Value
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Standard nominal flow rate	600 l/min
Adjustable delay time	0 s...30 s
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Type of mounting	With through-hole
Pneumatic connection	G1/8 G1/4
Note on materials	RoHS-compliant