


Piloted non return valve HGL-1/4-NPT

Part number: 34878

FESTO



Data sheet

Feature	Value
Valve function	Unlockable non-return function
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Type of mounting	Screw-in
Standard nominal flow rate	0 l/min...490 l/min
Operating pressure	0.03 MPa...1 MPa 0.3 bar...10 bar
Pilot pressure MPa	0.18 MPa...1 MPa
Pilot pressure	1.8 bar...10 bar
Pilot pressure psi	26.1 psi...145 psi
Ambient temperature	-20 °C...80 °C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-20 °C...80 °C
Note on materials	RoHS-compliant
Seals material	NBR