


Vacuum suction cup VASB-15-1/8-NBR

Part number: 35411

FESTO



Data sheet

Feature	Value
Nominal width	3 mm
Suction cup diameter	15 mm
Effective suction cup diameter	12 mm
Connection position	Top
Suction cup shape	Round bellows, 1.5 convolutions
Operating pressure	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-0.07 MPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-20 °C...80 °C
Breakaway force at 70% vacuum	7.9 N
Holding force at nominal operating pressure	7.9 N
Mounting thread	G1/8
Suction cup mounting	G 1/8
Vacuum connection	G1/8
Color	Black
Shore hardness	60 +/- 5
Material of screwed plug	Brass
Note on materials	RoHS-compliant
Suction cup material	NBR