

## Barbed elbow fitting LCNH-1/4-PK-6

Part number: 35989

**FESTO**



### Data sheet

| Feature   | Value  |
|---|--|
| Nominal width                                   | 4.9 mm   |
| Type of seal on screwed plug                    | Sealing ring   |
| Operating pressure for entire temperature range | -0.95 bar...10 bar   |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Information on operating and pilot media        | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                          | VDMA24364-B1/B2-L  |
| Ambient temperature                             | 0 °C...60 °C   |
| Pneumatic connection 1                          | External thread G1/4   |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 8 mm                         |
| Note on materials                               | RoHS-compliant   |
| Housing material                                | Aluminum<br>Die-cast zinc  |