

Barb tubing fitting

N-1/8-P-6

Part number: 3605

FESTO



Data sheet

Feature	Value
Nominal width	4.5 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Straight design
Pack size	10
Operating pressure for entire temperature range	-0.95 bar...16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque	5 Nm
Product weight	3.33 g
Pneumatic connection 1	External thread G1/8
Pneumatic connection 2	For tubing I.D. 6 mm
Note on materials	RoHS-compliant
Housing material	Aluminum, anodized