

Coupling piece KSZ-M8

Part number: 36124

FESTO



Data sheet

Feature	Value
Size	M8
Mounting position	Any
Threaded connection	Internal thread M8
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	70 g
Note on materials	RoHS-compliant
Mounting material	Steel Galvanized
Threaded coupling material	Steel Galvanized