


Quick coupling
EAMD-25-22-9-10X12
Part number: 3717923

FESTO



Data sheet

Feature	Value
Diameter of holder 1	9 mm
Diameter of holder 2	10 mm
Size	25
Nominal length	22 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	3.2 kgmm ²
Transferable torque	9 Nm
Product weight	43.2 g
Note on materials	RoHS-compliant