

# Adaptive gripper finger DHAS-GF-80-U-BU

Part number: 3998964

FESTO



## Data sheet

Feature	Value
Size	80
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
For use in the food industry	See supplementary material information
Ambient temperature	10 °C...50 °C
Product weight	13 g
Note on materials	RoHS-compliant
Clamping jaws material	TPE-U(PU)