

Quick coupling plug KS2-CK-3

Part number: 4091

FESTO



Data sheet

Feature	Value
Nominal width	2 mm
Operating pressure for entire temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Standard nominal flow rate	68 l/min...84 l/min
Nominal flow rate standardized according to ISO 8778	73.7 l/min...91.1 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:~:]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	4 g
Pneumatic connection 1	for pneumatic tubing outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut
Material of union nut	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Information on materials	Brass, nickel-plated