

Pressure gauge
OH-22-RT
Part number: 4131

FESTO



Data sheet

Feature	Value
Mounting position	Any
Operating pressure	1.4 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...45 °C
Ambient temperature	-10 °C...45 °C
Product weight	25 g
Type of mounting	Control panel installation in diameter 22.5
Pneumatic connection	G1/8
Note on materials	RoHS-compliant