

Profile mounting EAHF-L2-25-P-D2

Part number: 4759748

FESTO



Data sheet

Feature	Value
Size	25
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Product weight	24 g
Note on materials	RoHS-compliant
Plate material	Wrought aluminum alloy, anodized