

**Quick coupling**  
**EAMD-56-46-14-23X27**  
Part number: 5062229

**FESTO**



**Data sheet**

| Feature                | Value                 |
|------------------------|-----------------------|
| Diameter of holder 1   | 14 mm                 |
| Diameter of holder 2   | 23 mm                 |
| Size                   | 56                    |
| Nominal length         | 46.5 mm               |
| Mounting position      | Any                   |
| Max. rotational speed  | 5500 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C...60 °C        |
| Relative air humidity  | 0 - 95 %              |
| Ambient temperature    | -25 °C...60 °C        |
| Mass moment of inertia | 151 kgmm <sup>2</sup> |
| Transferable torque    | 38 Nm                 |
| Product weight         | 424 g                 |
| Note on materials      | RoHS-compliant        |