

Coupling
EAMD-42-40-16-16X25
Part number: 5153079

FESTO



Data sheet

Feature	Value
Diameter of holder 1	16 mm
Diameter of holder 2	16 mm
Size	42
Nominal length	40 mm
Mounting position	Any
Max. rotational speed	6000 rpm
Relative air humidity	0 - 95 %
Mass moment of inertia	39 kgmm ²
Transferable torque	17 Nm