

**Quick coupling**  
**EAMD-42-40-12-16X25**  
Part number: 5200241



**Data sheet**

| Feature                | Value                |
|------------------------|----------------------|
| Diameter of holder 1   | 12 mm                |
| Diameter of holder 2   | 16 mm                |
| Size                   | 42                   |
| Nominal length         | 40 mm                |
| Mounting position      | Any                  |
| Max. rotational speed  | 6000 rpm             |
| LABS (PWIS) conformity | VDMA24364-B2-L       |
| Storage temperature    | -25 °C...60 °C       |
| Relative air humidity  | 0 - 95 %             |
| Ambient temperature    | -25 °C...60 °C       |
| Mass moment of inertia | 39 kgmm <sup>2</sup> |
| Transferable torque    | 17 Nm                |
| Product weight         | 198 g                |
| Note on materials      | RoHS-compliant       |