


Quick coupling
EAMD-56-62-20-23X27
Part number: 5228153

FESTO



Data sheet

Feature	Value
Diameter of holder 1	20 mm
Diameter of holder 2	23 mm
Size	56
Nominal length	62.5 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	192 kgmm ²
Transferable torque	60 Nm
Product weight	507 g
Note on materials	RoHS-compliant