

Manifold
MHA3-PR8-3-1/8
Part number: 525224



Data sheet

Feature	Value
Max. no. of valve positions	8
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sub-base mounting type	With through-hole With H-rail
Pneumatic valve mounting type	With internal thread
Pneumatic connection 1/33	G1/4
Pneumatic connection 2	Internal thread G1/8
Pneumatic connection 3/11	G1/4
Material of sub-base	Wrought aluminum alloy