

Mounting kit
CRSMB-8-32/100
Part number: 525565

FESTO



Data sheet

Feature	Value
Size	8
Design	for round cylinders
Mounting position	Any
for piston Ø	Ø32 - Ø100
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
For use in the food industry	See supplementary material information
Degree of protection	IP65 IP68 IP69K
Ambient temperature	-40 °C...90 °C
Product weight	3 g
Type of mounting	Bonded
Note on materials	RoHS-compliant
Housing material	Aluminum, anodized TPE-U(PU)