

Intermediate position attachment SLG-Z-18-A

Part number: 525681

FESTO



Data sheet

| Feature | Value |
|--|--|
| Mounting position | Any |
| Structural design | Swivel module |
| Position sensing | For proximity sensor |
| Operating pressure | 1 bar...8 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 75 g |
| Type of mounting | With through-hole and dowel pin |
| Pneumatic connection | M3 |
| Stops material | Steel, nickel-plated |
| Seals material | PUR |
| Housing material | Aluminum Hard-anodized |