



# Pressure regulator MS4-LRB-1/4-D5-A8-AS

Part number: 529471

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Size                                     | 4  |
| Series                                   | MS   |
| Actuator lock                            | Rotary knob with detent<br>can be closed with accessories                          |
| Mounting position                        | Any  |
| Structural design                        | Directly controlled diaphragm regulator<br>with continuous compressed air supply   |
| Controller function                      | Outlet pressure constant<br>With secondary exhausting<br>With return flow function |
| Pressure gauge                           | G1/8 prepared  |
| Operating pressure                       | 0.8 bar...14 bar   |
| Pressure regulation range                | 0.3 bar...4 bar  |
| Max. pressure hysteresis                 | 0.25 bar   |
| Standard nominal flow rate               | 1900 l/min   |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]<br>Inert gas                         |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)                 |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Storage temperature                      | -10 °C...60 °C   |
| For use in the food industry             | See supplementary material information   |
| Temperature of medium                    | -10 °C...60 °C   |
| Ambient temperature                      | -10 °C...60 °C   |
| Product weight                           | 222 g  |
| Type of mounting                         | Front panel mounting<br>Line installation<br>With accessories<br>Optionally:       |
| Pneumatic connection 1                   | G1/4   |
| Pneumatic connection 2                   | G1/4   |
| Note on materials                        | RoHS-compliant   |
| Material of sub-base                     | Die-cast aluminum  |

| Feature                    | Value             |
|----------------------------|-------------------|
| Material of operator panel | PA<br>POM         |
| Seals material             | NBR               |
| Housing material           | Die-cast aluminum |
| Diaphragm material         | NBR               |