

Quick coupling plug KS4-1/2-I

Part number: 531680

FESTO



Data sheet

Feature	Value
Nominal width	7.85 mm
Operating pressure for entire temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Standard nominal flow rate	756 l/min...1314 l/min
Nominal flow rate standardized according to ISO 8778	819.5 l/min...1424.4 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Nominal tightening torque	32.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	57 g
Pneumatic connection 1	Internal thread G1/2
Note on materials	RoHS-compliant
Information on materials	Brass, nickel-plated