

Sealing ring OK-3/4

Part number: 531775

FESTO



Data sheet

Feature	Value
Based on norm	ISO 16030
Operating pressure for entire temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Manual tightening at RT	yes
Nominal tightening torque	35 Nm
Tolerance for nominal tightening torque	± 10%
Product weight	1 g
Pneumatic connection	G3/4
Note on materials	RoHS-compliant
Stops material	Reinforced PA
Seals material	TPE-U(PU)