

Electrical plug base MHAP-PI-1

Part number: 532182

FESTO



Data sheet

| Feature | Value |
|--|--------------------------|
| Type of mounting | Clip |
| Mounting position | Any |
| Product weight | 6 g |
| Electrical connection | 2-pin Socket |
| DC operating voltage range | 60 V |
| Current rating | 3 A |
| Cable length | 1 m |
| Cable diameter | 1 mm |
| Cable design | 2 x 0.14 mm ² |
| Degree of protection | IP40 |
| Ambient temperature | -20 °C...80 °C |
| Ambient temperature with flexible cable installation | -20 °C...50 °C |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Housing material | PA |
| Material of pin contacts | Copper alloy, tin-plated |