

Plug
FBS-SUB-9-BU-2X5POL-B
Part number: 532219

FESTO



Data sheet

Feature	Value
Width	20 mm
Height	62 mm
Length	61 mm
Protocol	CAN
Product weight	60 g
Fieldbus interface	2x 5 spring-loaded terminals
Note on fieldbus interface	BUS In - BUS Out looped through
Approved cable diameter	5 mm...10 mm
Degree of protection	IP65 IP67 In mounted state as per IEC 60529
Ambient temperature	0 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA-reinforced
Material of union nut	Brass
Material of screws	Steel
Seals material	NBR