


Fine filter combination LFMBA-3/4-D-MAXI-DA-A

Part number: 532881

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical +/- 5°
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	Fully automatic
Structural design	Fiber filter
Max. condensate volume	80 ml
Bowl guard	Metal bowl guard
Operating pressure	0.15 MPa...1.2 MPa 1.5 bar...12 bar 21.75 psi...174 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:7:2] Inert gas
Temperature of medium	1.5 °C...60 °C
Residual oil content	0.01 mg/m³
Ambient temperature	-10 °C...60 °C
Product weight	2362 g
Type of mounting	Line installation With accessories
Pneumatic connection 1	G3/4
Pneumatic connection 2	G3/4
Note on materials	RoHS-compliant
Compressed air filter material	Borosilicate fiber
Housing material	Die-cast zinc
Material of bowl	PC