

Power supply socket NTSD-WD-11

Part number: 533119

FESTO



Data sheet

Feature	Value
Type of mounting	With union nut
Mounting position	Any
Product weight	34 g
Electrical connection	4-pin Socket, angled Screw terminal
Operating voltage range AC	250 V
Current rating	16 A
Cable fitting	Pg11
Approved cable diameter	5 mm...11 mm
Connection cross section	2.5 mm ²
Degree of protection	IP67
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PBT
Material of pin contacts	Copper alloy Brass