

Sub-base
VMPA1-FB-AP-4-1
Part number: 533352



Data sheet

Feature	Value
Width	42 mm
Length	107.3 mm
Width dimension	10.5 mm
Max. no. of valve positions	4
Operating pressure	-0.9 bar...10 bar
Pilot pressure	3 bar...8 bar
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	185 g
Pneumatic connection 2	M7
Pneumatic connection 4	M7
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum