

Spiral plastic tubing PUN-12X2-SG-6-BL-3/8

Part number: 533467

FESTO



Data sheet

Feature	Value
Working length	6 m
Outside diameter	11.7 mm
Block length	1.312 m
Bending radius relevant for flow rate	65 mm
Inside diameter	7.9 mm
Winding diameter	51 mm
Number of windings	53
Temperature-dependent operating pressure	-0.95 bar...13 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...60 °C
Product weight	560 g
Pneumatic connection 1	External thread G3/8
Pneumatic connection 2	external thread G3/8
Color	Blue
Shore hardness	A 87 +/-3
Material of connecting thread	Brass Nickel-plated
Antikink device material	POM
Material of pneumatic tubing	TPE-U(PU)